

ISO 20379:2018-02 (E)

Fine ceramics (advanced ceramics, advanced technical ceramics) - Measurement of thixotropic behaviour of ceramic slurry by use of a rotational viscometer

Contents		Page
Foreword		iv
1	Scope	1
2	Normative references	1
3	Terms and definitions	1
4	Principle	2
4.1	Evaluation of thixotropic behaviour by hysteresis measurement of flow curve	2
4.2	Evaluation of thixotropic behaviour by time-dependence of shear stress at constant low shear rate	2
5	Apparatus	2
5.1	Measuring system	2
5.2	Basic capacity of the instrument	2
5.3	Calibration of rotational viscometer	3
5.4	Temperature control device	3
6	Pretreatment of the slurry samples	3
6.1	General	3
6.2	Degassing	3
6.3	Dispersion by stirring, mixing and ultrasonication	3
7	Measurement condition	3
7.1	Setting of ceramic slurry to rotational viscometer	3
7.2	Temperature	3
8	Measurement procedure	4
8.1	Measurement of thixotropic behaviour by hysteresis measurement of flow curve	4
8.1.1	Condition of shear rate and setting of measurement range	4
8.1.2	Measurement procedure	4
8.1.3	Analysis method of measurement results	4
8.2	Measurement of thixotropic behaviour by time-dependence of shear stress at constant low shear rate	5
8.2.1	Setting of measurement programme	5
8.2.2	Measurement procedure	5
8.2.3	Analysis method of measurement results	5
9	Test report	6
Bibliography		8